


## Flexible Coaxial Cable Assembly RG174 - SMB Straight Plug / SMB Straight Plug 202-5353-xxxxA



### List Nomenclature

- |   |                  |
|---|------------------|
| 1. SMB straight plug connector<br><i>With jack center contact</i> | B06344           |
| 2. Black Protective Sleeve  | A20130           |
| 3. Coaxial Cable  | A90066 (RG174/U) |

### Electrical Specifications

Impedance	:	50 ± 2 Ohms
Operating Frequency	:	DC to 3 GHz
Velocity of Propagation	:	66%
Voltage Withstand	:	1000 Veff

### Insertions Losses

Frequency (MHz)	50	500	1000	2000	3000
Insertions Losses max (dB/m)	0,45	1,08	1,61	2,25	2,90

### Mechanical Specifications

Inner Conductor	Multi-Brain WCS	7 x 0,16mm
Dielectric	PE	Ø = 1,52 mm (0,06 inches)
Outer conductor	Tinned copper 86% recovering	
Jacket	PVC	Ø = 2,80 mm (0,11 inches)
Static Bend Radius	:	9,80mm (0,385 inches)

### Environmental Specifications

Operating Temperature Range	:	-10°C à +80°C
-----------------------------	---	---------------

### Conditions of delivery

Mechanical check	:	Length
Electrical test	:	Continuity / Rigidity