

AUTO

106

# Core temperature thermometer

## testo 106 - The compact food thermometer

Ideal for use in the food sector

TopSafe: dishwasher-safe protective cover (IP65), protects from dirt and impact

Small, handy and always ready to hand

Audible and optical alarm

Automatic final value recognition (Auto-hold)

Hardly visible punctures

Certified according to EN 13485 (only in combination with TopSafe)

The core thermometer testo 106 is especially fast and robust. Its small handy shape means it is always close to hand and ready for use. Thanks to its very thin and robust measurement tip, it is excellently suited to core temperature checks in gastronomy, hotels, large kitchens, supermarkets etc. The dishwasher-safe TopSafe protects the instrument from dirt, water and impact. The testo 106 is comform to HACCP as well as EN 13485. If required, upper and lower limit values can be stored in the instrument; as soon as these values are violated, audible and optical warning signals are given. This alarm function and the automatic final value recognition facilitate measurement and support you in recognizing and interpreting measurement values quickly and correctly.

### www.testo.com

## **Technical data / Accessories**

	Sensor type	NTC	
testo 106	Meas. range	-50 to +275 °C	
testo 106, food core thermometer incl. probe protecting cap and battery	Accuracy ±1 digit	±1 % of mv (+100 to +275 °C) ±0.5 °C (-30 to +99.9 °C) ±1 °C (-50 to -30.1 °C)	
	Resolution	0.1 °C	
	General technical data		
Part no. 0560 1063	Storage temp.	-40 to +70 °C	
	Oper. temp.	-20 to +50 °C	
	t <sub>99</sub>	10 s	
	Battery type	3V button cell (CR 2032)	
	Battery life	350 h	
	Weight	80 g	
Set testo 106	Dimensions	215 x 34 x 19 mm	
	Length Probe shaft / Probe shaft tip	55 mm / 15 mm	
Set testo 106, food core thermometer incl. TopSafe (waterproof protection case, IP67, attachment clip, probe protection cap and	Diameter Probe shaft / Probe shaft tip	Ø 3 mm / Ø 2.2 mm	
battery	Display	LCD, 1 line	
Part no. 0563 1063	Material/Housing	ABS	
	Protection class	IP 67 with TopSafe	
	Warranty	2 years	

#### Accessories

Part	no.

#### Accessories for measuring instrument

TopSafe (indestructible protection case); waterproof and dishwasher-safe protection case (IP67)	0516 8265
Holding clip with probe protection cap	0554 0825
ISO calibration certificate/temperature ; for air/immersion probes, calibration point +60°C	0520 0063
ISO calibration certificate/temperature ; for air/immersion probes, calibration point -18°C	0520 0061
ISO calibration certificate/temperature ; for air/immersion probes, calibration point 0°C	0520 0062
ISO calibration certificate/temperature ; for air/immersion probes, calibration points -18°C; 0°C	0520 0041
ISO calibration certificate/temperature ; for air/immersion probes, calibration points -8°C; 0°C; +40°C	0520 0181

## www.testo.com