



**fitted with**

- work equipment**
- connected load**
- power consumption**
- luminous flux**
- luminous efficacy**
- light distribution**
- Beam Angle**
- light colour**
- color rendering index (CRI)**
- system of protection**
- class of protection**
- technology**
- usage**
- luminaire body**
- lamp cover**
- weight (net)**
- mains supply**

**LED**

- Energy efficiency category A+
- without
- 18-30 V; DC
- approx. 24 W
- approx. 1800 lm
- approx. 75 lm/W
- direct
- 80°/100°
- neutral white, approx. 5000 K
- > 80
- IP 67
- III
- switchable
- external
- aluminium, anodised, aluminium coloured anodised
- screen, clear
- approx. 2.1 kg
- built-in plug
- Serie\_763
- mounted version
- L-angle, clamp
- A=650 mm
- Power equipment

**design**

- fastening**
- dimension**
- special features**




Serie\_763

**illuminance**

Comment: d=100cm

Em: 657 lx  
 Emax: 856 lx  
 Emin: 408 lx



**luminous intensity**

