



Datasheet



ENGLISH

RS PRO 50mm Adhesive White Hook/Loop 5m roll

Stock No: 217-6999





Technical Specifications:

Sew-On/Hook	Sew-On/Loop
Base Material: Polyamide/Polyester Surface Yarn – Polyamide Ground Yarn – Polyester	Base Material: Polyamide/Polyester Surface Yarn – Polyamide Ground Yarn – Polyester
Construction: Standard with woven with cold – cut sewing edges.	Construction: Standard with woven with cold – cut sewing edges.
Width Tolerance: +/- 5%	Width Tolerance: +/- 5%
Weight: 305g/m ² (+/- 10%) depending on size of the roll.	Weight: 325g/cm ² (+/- 10%) depending on size of the roll.
Thickness: 1.85mm (+/- 0.5mm)	Thickness: 1.85mm (+/-0.5mm)

rspro.com

Quality Standards

Peel Strength ASTM D5170 / EN 13780	Average:
	
After 1 opening & closing cycle	1.2 N/cm
After 5000 opening & closing cycle	0.62 N/cm
After 10000 opening & closing cycle	0.43 N/cm

Shear Strength ASTM D5169 / EN 13780	Average:
	
After 1 opening & closing cycle	6.57 N/cm ²
After 5000 opening & closing cycle	5.59 N/cm ²
After 10000 opening & closing cycle	3.28 N/cm ²

Adhesive	Polacrylic modified, permanent (solvent free)
Adhesive thickness	0.24mm
Adhesive weight	230g/m²
Carrier	PES/PVA Diagonal Scrim
Liner	80 mic. Polyolefin Liner
Peel Adhesion	Min 30N/25mm (AFERA 5001)
Service temperature resistance.	-40°C to 100°C



rspro.com

