



SUPPORT DE RELAIS SLIM SLIM SOCKET

ESD01000

Compatible avec les relais électromécaniques et les relais statiques **celduc** sortie continue SLD et sortie alternative SLA.


Compatible with Electromechanical Relays and **celduc** solid state relays with DC output SLD and AC output SLA



celduc SSR References	Commande/ Input control A1 - A2	Sortie /Output COM - NO	Input Resistance R1 // R2 (Ohms)	Input Current
SLD01205	4,2-10VDC	24VDC 4A	300Ω	13mA @ 5VDC
SLD02205	8,2-20VDC	24VDC 4A	900Ω	12mA @ 12VDC
SLD03205	20-32VDC	24VDC 4A	1850Ω	12,5mA @ 24VDC
SLD01210	4,2-10VDC	48VDC 2,5A	300Ω	13mA @ 5VDC
SLD02210	8,2-20VDC	48VDC 2,5A	900Ω	12mA @ 12VDC
SLD03210	20-32VDC	48VDC 2,5A	1850Ω	12,5mA @ 24VDC
SLA01220	4,2-10VDC	12-280VAC 2A	300Ω	13mA @ 5VDC
SLA02220	8,2-20VDC	12-280VAC 2A	900Ω	12mA @ 12VDC
SLA03220	20-32VDC	12-280VAC 2A	1850Ω	12,5mA @ 24VDC

Proud to serve you

celduc®
r e l a i s





Raccordement/Connections

Section max de fil / Max. wire : 2,5 mm² / AWG 14

Tournevis / Screwdriver type : 2,5 x 0,5 mm

Couple de serrage /Screws torque : 0,5 Nm



6 mm

Plastique / Plastic Materials :

Material Designation: **Grilon TS V0**

Product Description: Polyamide 66/6 (PA66/6), designated "Grilon" furnished as pellets.

Color	Min. Thick. (mm)	Flame Class	HWI	HAI	RTI Elec	RTI Imp	RTI Str	IEC GWIT	IEC GWFI
ALL	0.4	V-0	4	0	125	-	-	-	-
	0.8	V-0	4	0	125	105	120	-	-
	1.5	V-0	3	0	125	105	120	-	960
	3.0	V-0	2	0	125	105	120	-	960

CTI: 0

IEC CTI: -

HVTR: 0

D495: 5

IEC Ball Pressure (°C): -

Dielectric Strength (kV/mm): -
ISO Tensile Strength (MPa): -
ISO Tensile Impact (kJ/m²): -

Volume Resistivity (10¹⁰ohm-cm): -
ISO Flexural Strength (MPa): -
ISO Izod Impact (kJ/m²): -

Dimensional Stability(%) : -
ISO Heat Deflection (°C) : -
ISO Charpy Impact (kJ/m²): -

Report Date: 2/24/1998

Underwriters Laboratories Inc®



celduc®
relais

www.celduc.com

5, Rue Ampère BP30004 42290 SORBIERS - FRANCE E-mail : celduc-relais@celduc.com
Fax +33 (0) 4 77 53 85 51 Service Commercial France Tél. : +33 (0) 4 77 53 90 20
Sales Dept.For Europe Tel. : +33 (0) 4 77 53 90 21 Sales Dept. Asia : Tél. +33 (0) 4 77 53 90 19