

# Double-poles Rocker Switch

**Q-1255**

TYPE: **SB-2041**

## SPECIFICATIONS

Contact Type: DPDT  
Rating: 10A 250V AC  
Contact R: 35mΩ max  
Insulation R: 500V DC 100MΩ min  
Dielectric Strength: 1 Minute 1500V AC  
Operating Temperature: -25°C ~ +85°C  
Electrical Life: 10, 000 Cycles

Outline Drawing

