

4 and 5-Pin Field Wireable Connectors, Standard Key

- IEC IP67 Protection



Housing Style	Female Part Number	Male Part Number	Features	Pinout
<p>B 81..</p>	<p>B 8141-0 B 8241-0</p>	<p>BS 8141-0 BS 8241-0</p>	<p>PBT, Black, PG 7 cable gland, accepts 4-6 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, 85°C, 250 V, 4 A, mates with standard key 4-pin cordsets and receptacles</p>	<p>Female</p> <p>Male</p>
<p>B 82..</p>	<p>B 8141-0/PG 9 B 8241-0/PG 9</p>	<p>BS 8141-0/PG 9 BS 8241-0/PG 9</p>	<p>PBT, Black, PG 9 cable gland, accepts 6-8 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, 85°C, 250 V, 4 A, mates with standard key 4-pin cordsets and receptacles</p>	<p>Female</p> <p>Male</p>
<p>BS 81..</p>	<p>B 8151-0/PG 9 B 8251-0/PG 9</p>	<p>BS 8151-0/PG 9 BS 8251-0/PG 9</p>	<p>PBT, Black, PG 9 cable gland, accepts 4-8 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, 85°C, 60 V, 4 A, mates with standard key 5-pin cordsets and receptacles</p>	<p>Female</p> <p>Male</p>
<p>BS 82..</p>	<p>BM 8151-0/PG 9</p>	<p>BS 8151-0/PG 9</p>	<p>PBT, Black, PG 9 cable gland, accepts 6-8 mm cable diameter, screw terminals, accepts up to 18 AWG conductors, metal coupling nut, 85°C, 60 V, 4 A, mates with standard key 5-pin cordsets and receptacles</p>	<p>Female</p> <p>Male</p>

Field Wireables