

KERN EOB300K100A



Die Klassiker unter den Paket- und Veterinärwaagen â auch mit XL-Plattform und großen Wägebereichen



Measuring system

Adjustment options:	External calibration
Linearity:	200 g
Readout [d]:	100 g
Recommended adjusting weight:	200 kg (M2)
Reproducibility:	100 g
Resolution:	3000
Stabilisation time:	3 s
Tare range:	300 kg
Warm up time:	10 min
Weighing range [Max]:	300 kg
Weighing system:	Strain gauge
Weighing units:	kg lb

Display

Display digit height:	2,500 cm
-----------------------	----------

Functions

Data hold function:	yes
Vibration-free weighing (Animal weighing program):	yes

Environmental conditions

Maximum humidity:	80 %
Maximum operating temperature:	35 °C
Minimum ambient temperature:	10 °C

Power supply

Input voltage:	220 V - 240 V AC 50 Hz
n/a:	CH EURO

n/a:	Mains adapter external
------	------------------------

Power supply

Operating time:	60 h
-----------------	------

Service

Adjustment at the location of installation: 961-249

DAkkS Certificate: 963-129

Category

Brand:	KERN
Category:	Balances
Product Group:	Platform scale

Packaging & shipping

Delivery:	24 h
Dimensions packaging (WxDxH):	476 x 416 x 120 mm
Gross weight:	5,500 kg
Net weight:	4,600 kg
Shipping method:	Parcel service

Construction

Cable length of display device:	1,800 m
Casing material:	plastic
Dimensions of display device (WxDxH):	212 x 110 x 45 mm
Dimensions of weighing plate (WxDxH):	315 x 305 x 55 mm
Material weighing plate:	stainless steel
Wall mount:	yes
Weighing surface (WxD):	315 x 305 mm