



**FAG****6214-2RSR**

Deep groove ball bearing

Schaeffler ID:  
0167211600000Deep groove ball bearing 62...-2RSR,  
single row, seals, steel sheet metal cage

## Technical information

**Main Dimensions & Performance Data**

d	70 mm	Bore diameter
D	125 mm	Outside diameter
B	24 mm	Width
$C_r$	66,000 N	Basic dynamic load rating, radial
$C_{0r}$	44,000 N	Basic static load rating, radial
$C_{ur}$	3,000 N	Fatigue load limit, radial
$n_G$	3,100 1/min	Limiting speed
	1.088 kg	Weight

**Mounting dimensions**

$d_{a \min}$	79 mm	Minimum diameter shaft shoulder
$D_{a \max}$	116 mm	Maximum diameter of housing shoulder
$r_{a \max}$	1.5 mm	Maximum fillet radius

**Dimensions**

$r_{\min}$	1.5 mm	Minimum chamfer dimension
$D_2$	110.7 mm	Caliber diameter outer ring
$d_1$	86.8 mm	Shoulder diameter inner ring

**Temperature range**

$T_{\min}$	-20 °C	Operating temperature min.
$T_{\max}$	100 °C	Operating temperature max.

**Calculation factors**

$f_0$	14.4	Calculation factor
-------	------	--------------------