


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.





REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	H	ECR-16-006855	18MAY2016	WL SY



- NOTES:
- MATERIAL:
    - HOUSING: PA6T, UL94V-0; COLOR: NATURAL.
    - CONTACTS: PHOSPHOR BRONZE.
    - PEGS: BRASS.
  - FINISH:
 

CONTACTS:  
GOLD FLASH ON ENTIRE CONTACT.  
(WITH ENTIRE CONTACT UNDERPLATED 50μ" MIN. NICKEL.)

PEGS: 100μ" MIN. MATTE-TIN OVER 50μ" MIN. NICKEL UNDERPLATED.
  - PART NUMBER OF MATING PLUG:  
MATING HEIGHT :  
3MM : X-1775014-X  
5MM : X-1775015-X  
5.5MM : X-1775149-X
  - REFLOW SOLDER CAPABLE TO 260°C PER TEC-109-201, CONDITION B.
  - SUBSTANCE RESTRICTIONS FOR LOW HALOGEN (BY WEIGHT):  
BROMINE (Br) ≤ 900 PPM (0.09%)  
CHLORINE (Cl) ≤ 900 PPM (0.09%)  
TOTAL CONCENTRATION OF (Cl) + (Br) ≤ 1500 PPM (0.15%)




12.8	13.8	11.1	10.3	8.8	24	1775013-2
E	D	C	B	A	NO. OF CONTACTS	PART NUMBER
DIMENSIONS						

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 19JUL2004	TE Connectivity BOARD-TO-BOARD CONNECTOR, 0.8mm PITCH, FINE-STACK RECEPTACLE			
DIMENSIONS: mm		CHK S. HOU 19JUL2004				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. KE 19JUL2004	NAME			
0 PLC ± -		PRODUCT SPEC		108-57488		
1 PLC ± 0.3		APPLICATION SPEC		-		
2 PLC ± 0.2		SIZE		A3		
3 PLC ± 0.15		CAGE CODE		00779		
4 PLC ± -		DRAWING NO		C-1775013		
ANGLES ± 2'		WEIGHT		0		
FINISH		RESTRICTED TO		-		
MATERIAL		CUSTOMER DRAWING		SCALE 7:1		
		SHEET 1 OF 2		REV H		


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



- NOTES:
- MATERIAL:  
 BOX: FIBREBOARD, CORRUGATED, DOUBLE WALL.  
 COVER TAPE: PET, TRANSPARENT COLOR.  
 CARRIER TAPE: POLYSTYRENES, BLACK COLOR.  
 REEL: PAPER, BROWN COLOR.  
 BAG: POLYETHYLENES, TRANSPARENT COLOR.
  - EACH BAG SHALL BE INCLUDED DESICCANT.
  - PEELING STRENGTH: 0.1~1.3 N (10~130 GRAMS).
  - PEELING SPEED: 300 mm/min.

1500	24.40	24.00	14.15	11.50	24
PCS / TAPE	W1	W	G	F	NO. OF CONTACTS
DIMENSIONS					

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 19JUL2004	 TE Connectivity BOARD-TO-BOARD CONNECTOR, 0.8mm PITCH, FINE-STACK RECEPTACLE											
DIMENSIONS: mm		CHK S. HOU 19JUL2004												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. KE 19JUL2004												
<table border="1"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± 0.3</td></tr> <tr><td>2 PLC</td><td>± 0.2</td></tr> <tr><td>3 PLC</td><td>± 0.15</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± 2'</td></tr> </table>		0 PLC				± -	1 PLC	± 0.3	2 PLC	± 0.2	3 PLC	± 0.15	4 PLC	± -
0 PLC	± -													
1 PLC	± 0.3													
2 PLC	± 0.2													
3 PLC	± 0.15													
4 PLC	± -													
ANGLES	± 2'													
MATERIAL		PRODUCT SPEC 108-57488	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO								
FINISH		APPLICATION SPEC	A3 00779		C=1775013	-								
-		WEIGHT 0	CUSTOMER DRAWING		SCALE 7:1	SHEET 2 OF 2								
					REV H									

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1775013-2](#)