

Tool set - CRIMPSET 25 - 1202580

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Assortment box, metal, supplied with ferrules acc. to DIN 46228-4, 300 pcs. AI 10-12 RD, 200 pcs. AI 16-12 BU, 100 pcs. AI 25-16 YE, as well as WIREFOX-D 40 stripping blade, CRIMPFOX 25R crimping pliers

Why buy this product

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools
-



Key commercial data

Packing unit	1 pc
GTIN	 4 017918 017934
Weight per Piece (excluding packing)	3050.3 g
Custom tariff number	82060000
Country of origin	Sweden

Technical data

Dimensions

Length (b)	206 mm
Height	48 mm
Width (a)	357 mm

General

Base element material	Metal
-----------------------	-------

Tool set - CRIMPSET 25 - 1202580

Articles in set

Ferrule - AI 10 -12 RD - 3200551



Ferrule, Sleeve length: 12 mm, Length: 22 mm, Color: red

Ferrule - AI 16 -12 BU - 3200564



Ferrule, Sleeve length: 12 mm, Length: 24 mm, Color: blue

Ferrule - AI 25 -16 YE - 3200577



Ferrule, Sleeve length: 16 mm, Length: 30 mm, Color: yellow

Stripping tool - WIREFOX-D 40 - 1212161



Stripping tool, for stripping cables of 4.5 mm - 40 mm-Ø, insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

Crimping pliers - CRIMPFOX 25R - 1212039



Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 10 mm² ... 25 mm², lateral entry, WM crimp

Classifications

eCl@ss

eCl@ss 4.0	21040301
eCl@ss 4.1	21040301

Tool set - CRIMPSET 25 - 1202580

Classifications

eCl@ss

eCl@ss 5.0	21043090
eCl@ss 5.1	21043090
eCl@ss 6.0	21049190
eCl@ss 7.0	21049190

ETIM

ETIM 2.0	EC000149
ETIM 3.0	EC000149
ETIM 4.0	EC000149
ETIM 5.0	EC000149

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC
