
$3M^{\text{TM}}$ Low Profile Header

$.100" \times .100"$ Straight and Right Angle, Four-Wall



- All over gold flash
- Sturdy body
- End windows
- Low cost
- Straight or right angle
- Ejector/latch option not available
- Regulatory Information: Visit 3M.com/regs or contact your 3M representative to find the RoHS compliance status of the 3M part you are interested in.

Date Modified: September 04, 2019

TS-0818 -D Sheet 1 of 3

Physical

Insu	lation:	
A A A A A A A A A A A A A A A A A A A		

Material: Glass Filled Polyester (PBT) Flammability: UL 94V-0 Color: Black **Contact:** Material: Brass **Plating:** Underplating: 30 μ" [0.76 μm] Nickel Wiping Area and Solder Tails: Gold Flash **Marking:** Orientation Triangle

Electrical

Environmental

Temperature Rating: -55°C to +105°C

Process Temperature: Maximum insulator temperature 191°C max, solder wave process only

UL File No.: E68080

ЗМ

Electronics Materials Solutions Division Interconnect Solutions http://www.3M.com/interconnect

3M[™] Low Profile Header

 $.100" \times .100"$ Straight and Right Angle, Four-Wall

Straight Table 1 Pin Dimensions -100 Ref [2.54] Quantity Α В 06 .60 [15.4] .51 [12.9] Position 2 —.108 [2.74] .61 [15.5] 08 .70 [17.8] 10 .80 [20.3] .71 [18.0] .015 [0.38] 14 1.00 [25.4] .91 [23.1] .33 16 1.10 [27.9] 1.01 [25.6] \Box [8.4] 20 1.30 [33.0] 1.21 [30.7] + 'n 1.60 [40.6] 1.51 [38.4] 26 100 Ref [2.54] 34 2.00 [50.8] 1.91 [48.5] 36 2.10 [53.6] 2.01 [51.0] .256 ± .008 -Position 1 [6.50] 2.30 [58.4] 2.21 [56.1] 40 Position 1 Orientation Triangle 50 2.80 [71.1] 2.71 [68.8] — .27 [6.86] .16 [4.1] Α .365±.010 .015 [9.3] [0.38] .025 ± .002 Sq Ref. [0.64] .25 [6.4] .236 ± .008 [5.99] Α A ± .02 110 ± .008 [2.79] .400 [10.16] Min End Stackable .250 [6.35] Distance 0 ò Min Side 100 Ref ø.040 ± .003 [1.02] -c C Stackable [2.54] Distance 197 [5.00] 0 c 0 0 Section A-A .100 ± .003 Inch [2.54] [mm] Position 1 as 100 ± .003 Tolerance Unless Noted indicated by [2.54] Triangle .0 .00 .000 Recommended P.C. Board Hole Pattern ±.005 ±.1 ±.01 Inch (Shown for mounting side of board.) [] Dimensions for Reference only Note 1: No ejector/latch option available. 2. Low temperature plastic. Check compatibility with "no lead" processing conditions prior to production use. **Ordering Information** 303XX - 6002HB (RIA E1 and C1 apply) HB - Gold Flash Pin Quantity: (See Table 1) TS-0818-D Sheet 2 of 3


ЗМ

Electronics Materials Solutions Division Interconnect Solutions http://www.3M.com/interconnect

303 Series

$3M^{TM}$ Low Profile Header

 $.100" \times .100"$ Straight and Right Angle, Four-Wall



ЗМ

Electronics Materials Solutions Division Interconnect Solutions http://www.3M.com/interconnect 3M is a trademark of 3M Company. For technical, sales or ordering information call 800-225-5373 Regulatory: For regulatory information about this product, visit 3M.com/regs or contact your 3M representative.

Technical Information: The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use: Many factors beyond 3M's control and uniquely within user's control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer: Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OR TRADE.

If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

3M Company Electronics Materials Solutions Division 13011 McCallen Pass, Bldg. C Austin, TX 78753-5380 1-800-225-5373 www.3M.com/interconnect



Electronics Materials Solutions Division Interconnect Solutions http://www.3M.com/interconnect

Please recycle. Printed in USA. © 3M 2019. All rights reserved. RIA-2217B-E