

Solder. Cut. Smooth.

Shadow-free LEDs help you take aim
on your most ambitious DIY projects



9400PKS Soldering Gun

Weller[®]



Cool LEDs!


Weller's new 9400PKS soldering gun features 3 cool LEDs that brightly illuminate your work without tip shadow, and a smooth, contoured grip with balanced housing that greatly reduces hand fatigue, allowing you to sharply focus on your soldering.

9400PKS



Guaranteed!

› 7-year warranty – the longest in the industry



Built-in ball guard protects cord

› The pivot of the ball prevents twisting and extends life of cord



“Rock and roll” grip foot

› Ergonomically-designed top to bottom – you can solder while resting and rocking the 9400PKS's rounded foot on your workbench.

The 9400PKS soldering gun at a glance...



6-second heat up

Tip is ready to solder almost immediately. No waiting!



3 built-in LEDs

- > Provide bright spotlight on your soldering joint
- > Eliminate tip shadow



Dual power trigger

140 W / 100 W

Two trigger positions control power at high to medium heat (up to 900 °F)



9400PKS Technical data

Dimensions (L x W x H)	300 x 275 x 65 mm 11.8 x 10.8 x 2.6 inches
Weight	810 grams / 1.8 lbs.
Power	140 W / 100 W
Temperature range	Up to 900 °F / 482 °C
Voltage input	120 V
Supplied tip(s)	7135 W, 6150, 6160
Heat-up time	6 seconds
Application light	3 LEDs
Duty	Heavy

Heating cycle

- › For intermittent usage
- › Trigger-pull heater activation
- › One minute on, 4 minutes off

Applications* for soldering, cutting and smoothing

› Heat sink › Ground plane › Metal art › Plumbing	› Hobby models › Small appliance › Small engine › Repair › Crafts	› Audio systems › Electrical › Marine › Jewelry › Automotive	› Soldering wire connections
●	◐	◐	< 4 AWG ∅ 0.20"

● Recommended ◐ Acceptable

*NOT RECOMMENDED FOR: microcomponents, electronic kits, low voltage wiring, pcbs, radio-controlled, indoor lighting



Also offering an extensive selection in professional soldering, filtration, and precision tools

Weller®

We're here to help!

weller-na@weller-tools.com

GERMANY

Weller Tools GmbH
Carl-Benz-Straße 2
74354 Besigheim

Tel: +49 (0) 7143 580-0
Fax: +49 (0) 7143 580-108

CHINA

Apex Tool Group
2nd Floor, Area C, 177 Bi Bo Road,
Pudong, Shanghai, 201203 P.R.C.

Tel: +86 (21) 60880288
Fax: +86 (21) 60880289

USA

Apex Tool Group, LLC
14600 York Rd., Suite A
Sparks, MD 21152

Tel: +1 (800) 688-8949
Fax: +1 (800) 234-0472

www.weller-tools.com

Weller® is a registered trademark of Apex Brands, Inc. | © 2017
ATG-3031 PDF only | Specifications subject to change without notice.