




BS 4174

450 HV



BN 30904

Pozi pan head tapping screws

with collar, form Z and cone end type C

Steel case-hardened 450 HV


zinc plated blue



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!

Further notice to residual risks can be found in the introduction section.

Article#	d ₁	d ₂ max.	k max.	c max.		m~	L
5000548	ST 2,9	6,53	1,6	0,8	1	2,9	6,5
5000556							9,5
5000521							13
5000610	ST 3,5	8,15	1,88	0,9	2	3,9	6,5
5000629							8
5000637							9,5
5000564							13
5000572							16
5000580							19
5000599							25
5000602							32
5000696	ST 4,2	9,75	2,36	1,1	2	4,3	8
5000718							9,5
5000645							13
5000653							16
5000661							19
5000688							25
5000750	ST 4,8	11,38	2,9	1,35	2	4,7	9,5
5000726							13
5000734							16
5000742							19
5000769	ST 5,5	13	3,15	1,6	3	6,2	16