INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 6WATT



STONTRONICS: T5885ST

Features:

- Interchangeable AC Heads
- 1 Year Warranty
- Level VI Efficiency
- Worldwide Approvals
- Safety approved to: UL62368-1, EN62368-1, UKCA62368-1 (Pending)



Description:

Our range of 6 Watt Interchangeable wall plug power supplies provide 6 Watts of continuous power with the flexibility of worldwide usage as they are supplied with UK, Euro & USA AC Heads, all Efficiency Level VI and carry worldwide safety approvals.


Specification	
Part Code	T5885ST
Input Voltage Range	90-264 Vac
Input Frequency Range	47-63Hz
Input Current Rated	300mA Max
Input AC Heads	UK, Euro & USA
Output Voltage Rating	+9V
Output Current Range	0.67A
Output Min Current	0.0A
Output Connection Type	2.1x5.5x12mm centre positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 3%
Ripple & Noise	<150mVp-p
Efficiency	79.0%Min
Over Voltage Protection	Output shut down and auto restart
Over Load Protection	Output shut down and auto restart
Operating Temperature	0°C to +40°C
Storage Temperature	-10°C to +70°C
Operating Humidity	20% to 80%
Storage Humidity	10% to 90%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	<0.25mA max
Safety Standard	UL/CUL, EN, CE, CB, GS, RCM, (UKCA pending)
EMI Standard	EN55022 C-TICK - AS/NZS CISPER22
MTBF	50K Hours
Size mm max.	64(L) x 40.5(W) x 30(H) mm
Weight	108 g


INTERCHANGEABLE WALL PLUG POWER SUPPLY 9VDC 6WATT



STONTRONICS: T5885ST

Diagrams





Tuning fork cannelure entire insulation type

© TT Electronics plc