

## 467BF - Metric hinged jointed combination wrenches




### Standards:

NF ISO 1711-1, NF ISO 691, ISO 1711-1, ISO 691, DIN ISO 1711-1, DIN ISO 691

### Description:

- Hinged head ratchet combination wrenches: to reach difficult access nuts.
- Compact ratchet mechanism and reversible by flipping the wrench.
- Increment 5° (6° for dimensions 8 and 9 mm).
- Ring head hinged at 180°.
- Open end head angled at 15°.
- Metric sizes: 8 to 19 mm.
- Presentation: satin chrome finish.

	A [mm]	Length L [mm]	Thickness E [mm]	Thickness E1 [mm]	Thickness E2 [mm]	Head Height C [mm]	Head Width B [mm]	Head Width B1 [mm]	Weight [Kg]
<b>467BF.10</b>	10.0	136.5	5.1	7.3	3.6	9.8	22.7	20.0	0.053
<b>467BF.11</b>	11.0	141.5	5.2	7.7	3.7	9.8	23.7	21.8	0.061
<b>467BF.12</b>	12.0	148.0	5.4	8.2	4.0	10.7	26.8	23.0	0.074
<b>467BF.13</b>	13.0	155.0	5.7	8.6	4.5	11.6	28.4	25.2	0.094
<b>467BF.14</b>	14.0	161.0	5.9	9.0	4.5	12.0	30.8	26.8	0.108
<b>467BF.15</b>	15.0	170.0	6.1	9.4	4.7	13.4	32.3	28.3	0.123
<b>467BF.16</b>	16.0	180.0	6.6	9.9	5.3	13.5	34.9	29.8	0.152
<b>467BF.17</b>	17.0	191.0	6.6	10.3	5.4	15.0	36.8	31.8	0.167
<b>467BF.18</b>	18.0	204.0	7.4	10.7	5.8	15.1	38.4	32.8	0.189
<b>467BF.19</b>	19.0	216.0	7.4	11.2	5.9	15.2	41.2	33.9	0.215
<b>467BF.7</b>	7								
<b>467BF.8</b>	8.0	127.5	4.6	6.5	3.1	8.0	18.6	16.7	0.038