




**SPECIFICATION
CONTROL DRAWING
Crystal Resonator**

FREQUENCY
48.000000MHz



Holder Style	25x2x05 4-pad
Mode	Fundamental
Adjustment Tolerance	± 20PPM at 25°C
Temperature Stability	± 20 PPM
Operating Temp. Range	-30°C to +85°C
Load Capacitance	10 pF
ESR	22 Max Ohm
Static Capacitance (C0)	Unspecified pF
Ageing	+/-2ppm/Yr Max
Marking	AEL48 WW/YY

Amdt Date	Change Note	AEL Code
		X48M000000S022
		Issue Ref A