



SPECIFICATION

- 1. Rated Noise Power0.15W
- 2. Max. Input Power0.3W
- 3. Rated Frequency Range700~50000Hz
- 4. Rated Frequency1200±200Hz
- 5. Rated Impedance8 Ω
- 6. Min. Sound Pressure Level.....83dB at 1.2KHz 1.1Vrms Sine Wave/10cm
- 7. Shell Material/ColorABS/Black
- 8. Operating Temperature-20~+60°C
- 9. Weight12g

No.	DESCRIPTION	APPROVED	DATE	KEPO NINGBO KEEP IMPROVING ELECTRONIC CO.,LTD http://www.chinaacoustic.com Magnetic Buzzer KPMB-3008A			
TOLERANCES: UNLESS NOTED OTHERWISE		APPROVALS	DATE				
XX.X	XXX.X	DRAWN					
90° ANGLES ±1°	FIRST ANGLE PROJECTION	CHECKED		UNIT	DWG NO.	K P3.840.619	
		APPROVED	03.01.15	SCALE		SHEET	VER. 1.0