





Subracks - *europac* **PRO** ServicePLUS

Universal EMC cover plates and mechanical protection

■ Used when PCBs with special dimensions are fitted

Order Information

 <p style="text-align: right;">06105082</p>	<p style="text-align: center;">Universal cover plate</p>  <p style="text-align: right;">06108079</p> <p>Al, 1.0 mm, hole diameter 4.0 mm, passivated, perforation degree 58 %, incl. lateral EMC sealing, incl. fixing screws</p>	<p style="text-align: center;">Stainless steel EMC gasket, between cover plate and horizontal rail</p>  <p style="text-align: right;">06106052</p> <p>stainless steel EMC gasket, clips into the horizontal rail and forms the contact with the cover plate; suitable for all horizontal rails</p>																																																																														
<table border="1"> <thead> <tr> <th>Width HP</th> <th>Depth mm</th> <th>Application</th> </tr> </thead> <tbody> <tr> <td>42</td> <td>175</td> <td>160 mm board depth</td> </tr> <tr> <td>42</td> <td>235</td> <td>160, 220 mm board depth</td> </tr> <tr> <td>42</td> <td>295</td> <td>160, 220, 280 mm board depth</td> </tr> <tr> <td>63</td> <td>175</td> <td>160 mm board depth</td> </tr> <tr> <td>63</td> <td>235</td> <td>160, 220 mm board depth</td> </tr> <tr> <td>63</td> <td>295</td> <td>160, 220, 280 mm board depth</td> </tr> <tr> <td>84</td> <td>175</td> <td>160 mm board depth</td> </tr> <tr> <td>84</td> <td>235</td> <td>160, 220 mm board depth</td> </tr> <tr> <td>84</td> <td>295</td> <td>160, 220, 280 mm board depth</td> </tr> <tr> <td>84</td> <td>355</td> <td>160, 220, 280 mm board depth</td> </tr> <tr> <td>84</td> <td>415</td> <td>160, 220, 280 mm board depth</td> </tr> <tr> <td>84</td> <td>475</td> <td>160, 220, 280 mm board depth</td> </tr> </tbody> </table>	Width HP	Depth mm	Application	42	175	160 mm board depth	42	235	160, 220 mm board depth	42	295	160, 220, 280 mm board depth	63	175	160 mm board depth	63	235	160, 220 mm board depth	63	295	160, 220, 280 mm board depth	84	175	160 mm board depth	84	235	160, 220 mm board depth	84	295	160, 220, 280 mm board depth	84	355	160, 220, 280 mm board depth	84	415	160, 220, 280 mm board depth	84	475	160, 220, 280 mm board depth	<table border="1"> <thead> <tr> <th>PU 1 pair</th> <th>PU 10 pieces</th> <th>PU 100 pieces</th> </tr> </thead> <tbody> <tr> <td>24560-031</td> <td></td> <td></td> </tr> <tr> <td>24560-032</td> <td>24560-241</td> <td>–</td> </tr> <tr> <td>24560-033</td> <td></td> <td></td> </tr> <tr> <td>24560-041</td> <td></td> <td></td> </tr> <tr> <td>24560-042</td> <td>24560-243</td> <td>–</td> </tr> <tr> <td>24560-043</td> <td></td> <td></td> </tr> <tr> <td>24560-051</td> <td></td> <td></td> </tr> <tr> <td>24560-052</td> <td></td> <td></td> </tr> <tr> <td>24560-053</td> <td>24560-245</td> <td>24560-246</td> </tr> <tr> <td>24560-054</td> <td></td> <td></td> </tr> <tr> <td>24560-055</td> <td></td> <td></td> </tr> <tr> <td>24560-056</td> <td></td> <td></td> </tr> </tbody> </table>	PU 1 pair	PU 10 pieces	PU 100 pieces	24560-031			24560-032	24560-241	–	24560-033			24560-041			24560-042	24560-243	–	24560-043			24560-051			24560-052			24560-053	24560-245	24560-246	24560-054			24560-055			24560-056			
Width HP	Depth mm	Application																																																																														
42	175	160 mm board depth																																																																														
42	235	160, 220 mm board depth																																																																														
42	295	160, 220, 280 mm board depth																																																																														
63	175	160 mm board depth																																																																														
63	235	160, 220 mm board depth																																																																														
63	295	160, 220, 280 mm board depth																																																																														
84	175	160 mm board depth																																																																														
84	235	160, 220 mm board depth																																																																														
84	295	160, 220, 280 mm board depth																																																																														
84	355	160, 220, 280 mm board depth																																																																														
84	415	160, 220, 280 mm board depth																																																																														
84	475	160, 220, 280 mm board depth																																																																														
PU 1 pair	PU 10 pieces	PU 100 pieces																																																																														
24560-031																																																																																
24560-032	24560-241	–																																																																														
24560-033																																																																																
24560-041																																																																																
24560-042	24560-243	–																																																																														
24560-043																																																																																
24560-051																																																																																
24560-052																																																																																
24560-053	24560-245	24560-246																																																																														
24560-054																																																																																
24560-055																																																																																
24560-056																																																																																
<p>Assembly tool, for EMC gasket, stainless steel (horizontal rails), 1 piece</p> 	<p style="text-align: center;">–</p>	<p style="text-align: center;">24560-271</p>																																																																														