






RoHS

THIS IS A RoHS  
COMPLIANT  
COMPONENT/  
PRODUCT.



NOTES:

ELECTRICAL:

- 1. VOLTAGE RATING : 125 VAC.
- 2. CURRENT RATING : 1.5 AMP.
- 3. CONTACT RESISTANCE : 100 MILLIOHMS MAX.
- 4. INSULATION RESISTANCE : 1000 MEGOHMS MIN. @ 500 VDC.
- 5. DIELECTRIC STRENGTH : 750 VAC 60Hz, 1MIN.

MECHANICAL:

- 1. HOUSING MATERIAL : PC UL94V-0, WHITE
- 2. INSERT MATERIAL : PBT+30% GF. UL94V-0
- 3. PCB MATERIAL : FR-4 THICKNESS 1.6mm
- 4. CONTACT MATERIAL : PHOSPHOR BRONZE
- 5.IDC CONTACT MATERIAL : PHOSPHOR BRONZE t=0.50mm WITH NICKEL PLATING
- 6.WIRE : #24~26 AWG

ENVIRONMENTAL:

- 1. STORAGE : -40°C TO +85°C.
- 2. OPERATION : -40°C TO +85°C.

MARK	000000	NEW DESIGN	HENRY	120617'
	ECN-NO.	REVISION RECORD	DRAWN	DATE
	UNLESS OTHERWISE SPECIFIED TOLERANCE		SCALE	CHECKED
	Dimension Range	Tolerance	1/1	APPROVED
	X.X	±0.20	UNIT	
	X.XX	±0.15	mm	
	X.XXX	±0.10	SIZE	A3
	ANGLE	±5°		SHEET 1/1
Material/Plated/Notes		NAME		
SEE NOTE		SIDE ENTRY KEYSTONE , C6		
Tooling No.	PART NO. 326I-0020-0I		REV. 0	
	DOC. NO.			