








RoHS

THIS IS A RoHS COMPLIANT COMPONENT/PRODUCT.



NOTES:

ELECTRICAL:

- 1. VOLTAGE RATING : 125 VAC RMS.
- 2. CURRENT RATING : 1.5 AMP.
- 3. CONTACT RESISTANCE : 100 MILLIOHMS MAX.
- 4. INSULATION RESISTANCE : 1000 MEGOHMS MIN. @ 500 VDC.
- 5. DIELECTRIC STRENGTH : 750 VAC RMS 60Hz, 1MIN.
- 6. C6 PERMANENT LINK : CONFORM TO ANSI/TIA/EIA-568 B.2

MECHANICAL:

- 1. HOUSING MATERIAL : PC UL94V-0
- 2. INSERT MATERIAL : FLAME RETARDANCY ABS UL94V-0
- 3. PCB MATERIAL : FR-4 THICKNESS 1.6mm
- 4. CONTACT MATERIAL : PHOSPHOR BRONZE STAMP PIN t=0.35mm
- 5. IDC CONTACT MATERIAL : PHOSPHOR BRONZE t=0.50mm WITH TIN PLATING
- 6. WIRE : AWG 24~26

ENVIRONMENTAL:

- 1. STORAGE : -40°C TO +85°C.
- 2. OPERATION : 0°C TO 70°C.

CONFORM TO TIA/EIA 568B
 MATES WITH MODULAR PLUG CONFORMING TO
 FCC PART 68, SUBPART F.

ADD THE COLOR OF LABEL		SAIL	031007
NEW DESIGN		SAIL	120406
MARK	ECN-NO.	REVISION RECORD	DRAWN DATE
		UNLESS OTHERWISE SPECIFIED TOLERANCE	SCALE 1/1
		CHECKED Eva	APPROVED David
Material/Plated/Notes		NAME	CAT.6 KEYSTONE, 6u" FTP
SEE NOTE		PART NO.	3261-0014-02
Tooling No.		DOC. NO.	REV. B