










Ø 2 mm – Ø 2.5 mm

Order No.	Type	Nominal-Ø	Type of termination	Metal parts / plating	Withdrawal force	Max. temperature	Rated current ¹⁾	Contact resistance	Assembly material, order separately	
		mm			N	°C	A	mΩ		
22.1100	SA200	2	M2	CuZn, Au	~4	150	25	0.4	p. 16	
22.1102	SA200N	2	M2	CuZn, Ni	~4	150	25	2	p. 16	 
22.6303	SA203	2	Soldering	CuZn, Ni	~4	150	25	2		 
22.5118	SA2,5	2.5		CuZn, Au	~6	150	25	0.5		 
22.5117	SA2,5-G	2.5	M2,5	CuZn, Au	~6	150	25	0.5		 

¹⁾ According to connecting method and cross section