














ТПП-40

Наименование, мощность (P), Вт	Входное напряжение	Выходное напряжение В	Ток нагрузки I (А)	Выходное напряжение х.х. В	Мах Ток Холостого Хода мА	Габаритный размер	КПД	Фото
ТПП-40	230	6	6,67	6,67	5	75/30-42	0,89	
	230	9	4,4	10,01	5	75/30-42	0,89	
	230	12	3,3	13,34	5	75/30-42	0,89	
	230	15	2,67	16,68	5	75/30-42	0,89	
	230	18	2,2	20,01	5	75/30-42	0,89	
	230	24	1,67	26,68	5	75/30-42	0,89	
	230	2x6	3,3	2x6,67	5	75/30-42	0,89	
	230	2x9	2,2	2x10,01	5	75/30-42	0,89	
	230	2x12	1,67	2x13,34	5	75/30-42	0,89	
	230	2x15	1,3	2x16,68	5	75/30-42	0,89	
	230	2x18	1,1	2x20,01	5	75/30-42	0,89	
	230	2x18	1,1	2x20,01	5	75/30-42	0,89	
	230	2x24	0,83	2x26,68	5	75/30-42	0,89	
	230	220	0,18	244,57	5	75/30-42	0,89	