



THIS IS A RoHS
COMPLIANT
COMPONENT/
PRODUCT.

REFERENCE

NOTES:

ELECTRICAL:







1. VOLTAGE RATING: 125 VAC RMS.
2. CURRENT RATING: 1.5 AMP.
3. CONTACT RESISTANCE: 100 MILLIOHMS MAX.
4. INSULATION RESISTANCE: 1000 MEGOHMS MIN @ 500 VDC.
5. DIELECTRIC STRENGTH: 750 VAC RMS 60Hz,1MIN.
6. C6A CONNECTING: CONFORM TO ANSI/TIA/EIA-568 C.2

ENVIRONMENTAL:

1. STORAGE: -40°C TO +85°C.
2. OPERATION: -40°C TO +85°C.

MECHANICAL:

1. HOUSING MATERIAL: UL94V-0
2. INSERT MATERIAL: UL94V-0
3. PCB MATERIAL: FR-4
4. CONTACT MATERIAL: PHOSPHOR BRONZE
5. IDC CONTACT MATERIAL: PHOSPHOR BRONZE WITH SILVER OR NICKEL PLATING
6. WIRE : AWG 23~26



△X0	006900	NEW DESIGN	PETER	0911'17
MARK	ECN-NO.	REVISION RECORD	DRAWN	DATE
	UNLESS OTHERWISE SPECIFIED TOLERANCE		SCALE	CHECKED
	Dimension Range Tolerances		1:1	APPROVED
	X.X	±0.20	UNIT	mm
	X.XX	±0.15	SIZE	
	X.XXX	±0.10	SIZE	A3
ANGLE	±5°			
Material/Plated/Notes		NAME		
SEE NOTE		CAT.6A TOP ENTRY SLIM TYPE KEYSTONE FTP JACK		
Tooling No.		PART NO.	326I-0006-05	REV.
		DOC. NO.		1

