

This is a sample photo.

**ORDER SYMBOL:** PCT 233009

**EL.number** **EAN:** 6418074003829

Sweden:  
Denmark: 8212003017  
Finland: 3423544

**INCLUDING:**

Enclosure body, cover with PUR gasket, cover screws, and mounting screws.


**APPROVALS:**

USA: UL Type 1, 4, 4X, 12, 13 (E75645 Vol.1 Sec.6); IK 08 (front) IK 07 (side) (IK-code EN50102); UL 94-V2

EURO: IP 67/IP 66; IK 08 (front) IK 07 (side) (IK-code EN50102); UL 94-V2

OTHERS: IEC 529, CE, EEI, FIMKO 189830-01

FIBOX EURONORM II PC



**TECHNICAL INFORMATION:**

Standard colour: RAL 7035  
Ingress protection: IP 67 (IEC 529)  
Flame resistance: UL 94-V2

Temp.range in cont. use: Max. +80 °C  
Temp. range of material: - 40 °C - + 120 °C

**ACCESSORIES**

|               |          |          |          |
|---------------|----------|----------|----------|
| Fastening lug | TF 28037 | DIN-Rail | TRM 0812 |
| DIN-Rail      | TRH 1212 | DIN-Rail | TRM 0816 |
| DIN-Rail      | TRH 1216 | DIN-Rail | TRM 1212 |
| DIN-Rail      | TRH 1220 |          |          |
| DIN-Rail      | TRH 1520 |          |          |
| DIN-Rail      | TRH 2330 |          |          |
| DIN-Rail      | TRH 24   |          |          |
| DIN-Rail      | TRM 0507 |          |          |
| DIN-Rail      | TRM 0808 |          |          |