

HUBER+SUHNER® DATA SHEET

Coaxial Cable Connector: 24_QMA-50-2-1/111_N

Rev.: C



Description

Straight panel bulkhead cable jack, flange mount

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Centre contact plugged
Outer contact soldered
Weight 0.0041 kg

Environmental Data

Operating Temperature -40 °C to 85 °C
2002/95/EC (RoHS) compliant

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE
Gasket	MVQ (Silicone Rubber)
Fastening nut	Brass
Washer	Bronze

Surface Plating

SUCOPRO Plating
SUCOPRO Plating
SUCOPRO Plating
SUCOPRO Plating
SUCOPRO Plating
SUCOPRO Plating

Related Documents

Outline drawing	DOU-00009765
Catalogue drawing	DCA-00009767
Assembly instruction	DOC-0000179521
Mounting hole	DOU-00008748

Ordering Information

Single package	24_QMA-50-2-1/111_NE
Bulk 100 pcs package	24_QMA-50-2-1/111_NH

Additional Information

Suitable cables SUCOFORM_86, EZ_86_TP_M17, MULTIFLEX_86

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions