

Section Links

A045 | A040 | A095 | A090 | A195 | A190 | **A080** | A085 | A087 | A200 | A070 | A210 | A300 | A315 | A089 | A125 | A105 | A205

Product Details

A080 Stainless Steel Base and Stud

Materials Base - Stainless Steel, Type 303
Stud - Stainless Steel, Type 303



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Overall Height H (mm)	Maximum Recommended Load (kg)
A080/003	M8	30	38	55	450
A080/002	M8	60	38	85	450
A080/004	M10	75	38	100	600
A080/041	M12	75	38	100	1000
A080/042	M12	125	38	150	1000
A080/014	M12	75	55	105	1500
A080/015	M12	125	55	155	1500
A080/005	M12	150	55	180	1500
A080/016	M16	75	70	114	2000
A080/020	M16	125	70	164	2000
A080/006	M16	150	70	189	2000
A080/008	M16	200	70	239	2000
A080/039	M20	125	100	177	3000
A080/007	M20	150	100	202	3000
A080/009	M20	200	100	252	3000
A080/040	M24	125	100	181	4000
A080/010	M24	150	100	206	4000
A080/012	M24	200	100	256	4000
A080/011	M24	250	100	306	4000

Dimensions are approximate

