


Housing



Circuits	Model No.		Dimensions mm(in.)		Qty / bag	
	Standard type	Retainer mountable type	A	B	Standard type	Retainer mountable type
2	XAP-02V-1	XARP-02V	2.5 (.098)	7.3 (.287)	1,000	1,000
3	XAP-03V-1	XARP-03V	5.0 (.197)	9.8 (.386)	1,000	1,000
4	XAP-04V-1	XARP-04V	7.5 (.295)	12.3 (.484)	1,000	1,000
5	XAP-05V-1	XARP-05V	10.0 (.394)	14.8 (.583)	1,000	1,000
6	XAP-06V-1	XARP-06V	12.5 (.492)	17.3 (.681)	1,000	1,000
7	XAP-07V-1	XARP-07V	15.0 (.591)	19.8 (.780)	1,000	1,000
8	XAP-08V-1	XARP-08V	17.5 (.689)	22.3 (.878)	1,000	1,000
9	XAP-09V-1	XARP-09V	20.0 (.787)	24.8 (.976)	1,000	1,000
10	XAP-10V-1	XARP-10V	22.5 (.886)	27.3 (1.075)	1,000	1,000
11	XAP-11V-1	XARP-11V	25.0 (.984)	29.8 (1.173)	1,000	1,000
12	XAP-12V-1	XARP-12V	27.5 (1.083)	32.3 (1.272)	1,000	1,000
13	XAP-13V-1	XARP-13V	30.0 (1.181)	34.8 (1.370)	1,000	1,000
14	XAP-14V-1	XARP-14V	32.5 (1.280)	37.3 (1.469)	500	1,000
15	XAP-15V-1	XARP-15V	35.0 (1.378)	39.8 (1.567)	500	1,000
18	—	XARP-18V	42.5 (1.673)	47.3 (1.862)	—	500
20	XAP-20V-1	—	47.5 (1.870)	52.3 (2.059)	500	—

Material

Nylon 66, UL94V-0, natural (white)

<For reference> As the color identification, the following alphabet shall be put in the underlined part.
For availability, delivery and minimum order quantity, contact JST.

<Standard type>


ex. **XAP-02V-1-aa**
(blank)...natural (white)
K...black R...red E...blue Y...yellow L...lemon yellow M...green
O...orange N...brown H...gray P...purple LE...light blue
PK...pink FY...vivid yellow Z...ivory

<Retainer mountable type>

ex. **XARP-02V-aa**
(blank)...natural (white)
K...black R...red E...blue L...lemon yellow

10R JST

Retainer



Circuits	Model No.	A	Qty / bag
2	XMS-02V	2.5 (.098)	1,000
3	XMS-03V	5.0 (.197)	1,000
4	XMS-04V	7.5 (.295)	1,000
5	XMS-05V	10.0 (.394)	1,000
6	XMS-06V	12.5 (.492)	1,000
7	XMS-07V	15.0 (.591)	1,000
8	XMS-08V	17.5 (.689)	1,000
9	XMS-09V	20.0 (.787)	1,000
10	XMS-10V	22.5 (.886)	1,000
11	XMS-11V	25.0 (.984)	1,000
12	XMS-12V	27.5 (1.083)	1,000
13	XMS-13V	30.0 (1.181)	1,000
14	XMS-14V	32.5 (1.280)	1,000
15	XMS-15V	35.0 (1.378)	1,000

Material

Glass-filled nylon 66, UL94V-0, natural (ivory)