

IBG 06MTL

- Part number : IBG 06MTL
- Color code : Blue
- Body : Composite
- Nozzle : Metal
- Triger : Progressive
- Connection : ISO 6150 B 6mm
- Maxi temperature : +70°C
- Mini temperature : -15°C
- Impossible dust intrusion
- Concentrated blowing
- Non scratch body
- Crush resistant
- Flow @ 6 b : 20 m³/h - 11.76 cfm
- Sound level : 89 db
- Blowing force : 88 g
- Dynamic pressure : 2.2 b
- Weight : 88 g
- Advised coupling ISI 06

