

POWER SUPPLIES S-10 Series



Features

- Slim design
- High efficiency, up to 85%
- Low no load power consumption
- Class II, wide range input (85-265VAC)
- Protections: overheating, short circuit, overload, overvoltage, supply voltage interruption
- LED indicator for power on
- DIN rail mountable



Technical data

MODEL		S-10-05	S-10-10	S-10-12	S-10-24
OUTPUT	DC VOLTAGE	5V	10V	12V	24V
	RATED CURRENT	2A	1A	0.8A	0.4A
	VOLTAGE TOLERANCE	+ - 2%	+ - 2%	+ - 2%	+ - 2%
	RATED POWER	10W	10W	10W	10W
	RIPPLE & NOISE	80mVp-p	120mVp-p	120mVp-p	150mVp-p

INPUT	VOLTAGE RANGE	85 ~ 265VAC 90 ~ 385VDC
	FREQUENCY RANGE	47 ~ 63Hz
	EFFICIENCY	85%
	AC CURRENT	0.5A/115VAC 0.25/230VAC
WORKING TEMP. / HUMIDITY		-20 ~ 60°C / 20 ~ 90% RH

Dimensions

