



ELECTRICAL TEST:

100% simulated test using apple computer



PIN Assignment



13	Mini DP Male ABS Front Housing BLACK	1	PCS
12	Mini DP Male ABS Housing BLACK	1	PCS
11	Mini DisplayPort Male,Terminal:GOLD PLATED,White INSULATION,SHELL:NI Plated	1	PCS
10	LINE CLIP:Mini DisplayPort Male 32AWG	1	PCS
9	#4-40UNC H4.75*8.6mm NI Plated, Nut (H=4.8mm)	2	PCS
8	OD:0.8mm Black Heat Shrinkable TUBE L:6mm*3pcs L:8mm*2pcs	0.018	M
7	mini Display Port M PVC Transparent Dust Cover	1	PCS
6	VGA Female Connector ABS Front Housing BLACK	1	PCS
5	VGA Female Connector ABS Housing BLACK MARK:VGA	1	PCS
4	LD-PE Transparent	6	G
3	65P BLACK PVC	12	G
2	MDPV12-15CM PCB+SMT(NI Plated) PCB	1	PCS
1	UL20276[34AWG(7/0.06TC)*1P+EAM]*5C+32AWG(7/0.08TC)*5C+AEB (16/5/0.12MM 85%AL) OD:4.5MM Black	0.21	M
NO	DESCRIPTION	Q'TY	UNIT

REV.	ECN NO.:	DESCRIPTION	DATE	HANDLE
		TOLERANCE INCHES M/M		
.X	.015	.30		
.XX	.010	.10		
.XXX	.005	.05		
DRAWN BY		DXM	TITLE: Mini Display Port to VGA Female L:0.15M	
CHECK BY			CUSTOMER :	CPC
APPD BY			CUSTOMER P/N :	CS26508
SCALE	NONE	DRAWING NO.:		REV. A01
UNIT	MM	CAC250192		1/1
DATE	13.03.09			