




Eterna WGLEDBK/WH

9.50 kWh/1000h

This luminaire is compatible with bulbs of the energy classes:




This luminaire is sold with a bulb of the energy class: **A+**

874/2012



LED WELL GLASS FITTING WITH PC DIFFUSER & OPTIONAL CORNER BRACKET

- Requires 1 x LED ES lamp (included). Fitting is rated at 23W max
- This luminaire is compatible with bulbs of the energy classes: A+ to E and is sold with a bulb of the energy class: A+
- Bracket included for optional corner mounting: complete solution for flat wall or corner mounting
- Aluminium alloy in white or black finish with white polycarbonate diffuser
- Low energy consumption and prolonged lamp life
- BESA box mounting



Shown with Optional Corner Brackets

• M.O.M: 1 / O.P.Q: 4

Code	Version	Colour	Wattage	Colour Temp.	Lumens	Avg. Rated Life (Hrs)	IP Rating	Energy Rating
WGLEDBK	Fitting	Black	9.5W	2700K	806 lm	15,000 hrs	IP65	A+
WGLEDWH	Fitting	White	9.5W	2700K	806 lm	15,000 hrs	IP65	A+
WELLDIFF	Diffuser	White	-	-	-	-	-	-



LAMP SPECIFICATIONS:

Nominal luminous flux	806 lm
Rated Wattage	9.5W
Rated luminous flux	806 lm
Nominal life time of the lamp	15,000 hrs
Colour temperature	2700K
Number of switching cycles before premature lamp failure	100,000
Warm-up time up to 60 % of the full light output	Instant full light
Dimmable	No
Lamp dimensions (L/Ø)	110x60mm
Nominal beam angle	220°
Cap type	ES (E27)
Rated power	9.5W
Rated lamp lifetime	15,000 hrs
Lamp power factor	≥0.5
Lumen maintenance factor at end of nominal life	>70%
Starting time	Instant full light
Colour rendering	>80 Ra
Colour consistency	Within 6 step Macadam ellipse
Rated beam angle	220°
Voltage	240V
Frequency Hz	50Hz