

## ToLEDo Retro A60

ToLEDo RT A60 470LM B22 SL

0027162



### Product features

- 



### PRODUCT OVERVIEW

Lamp finish	Clear
Lamp shape	GLS
Colour temperature (K)	2700
CRI (Ra)	80
Dimmable	No
EAN code	5410288271620
Energy class	A++
Equivalent watt (W)	40
Cap/Base	B22
Type	ToLEDo Retro A60
Watt (Nominal) (W)	4
Light colour	Homelight
Ordering number	0027162
Efficacy (Rated) (lm/w)	117.5
Average life (h) - L70/B50	15000
Luminous flux (Rated) (lm)	470
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

### DATA TABLE

#### General data

Average life (h) at Ta 25° C	15000
Control gear required	No
Lamp finish	Clear
Lamp shape	GLS
Dimmable	No

## ToLEDo Retro A60

ToLEDo RT A60 470LM B22 SL

**0027162**

<b>Dry applications use only</b>	Yes
<b>EAN code</b>	5410288271620
<b>Energy class</b>	A++
<b>Energy saving lamp</b>	Yes
<b>General application</b>	Hospitality; Residential & Consumer
<b>Intended purpose</b>	No
<b>Cap/Base</b>	B22
<b>Lamp mercury content (mg)</b>	0
<b>Type</b>	ToLEDo Retro A60
<b>No. of switching cycles before premature failure (min)</b>	>50,000
<b>Optimal operating condition (°C)</b>	25
<b>Ordering number</b>	0027162
<b>Product name</b>	ToLEDo RT A60 470LM B22 SL
<b>Average life (h) - L70/B50</b>	15000
<b>Special purpose lamp</b>	No
<b>Starting time (max) (s)</b>	0.05
<b>Technology</b>	LED
<b>Transformer required</b>	No
<b>Warm-up time to 60% of full light (max) (s)</b>	< 1s => 60%
<b>E-number SE</b>	8290505

### Optical data

<b>Colour temperature (K)</b>	2700
<b>CRI (Ra)</b>	80
<b>Light colour</b>	Homelight
<b>Lumen maintenance at end of nominal life (%)</b>	80
<b>Luminous flux (Nominal) (lm)</b>	470
<b>Luminous flux (Rated) (lm)</b>	470
<b>Suitable for accent lighting</b>	No
<b>Adjustable chromaticity</b>	No
<b>Colour consistency (SDCM)</b>	6

### Electrical data

<b>Current (A)</b>	38
<b>Drive current (mA)</b>	38
<b>Equivalent watt (W)</b>	40
<b>kWh per 1000 hours burning time</b>	4
<b>Lamp power factor</b>	0.5
<b>Watt (Nominal) (W)</b>	4
<b>Efficacy (Rated) (lm/w)</b>	117.5
<b>Watt (Rated) (W)</b>	4

## ToLEDo Retro A60

ToLEDo RT A60 470LM B22 SL

**0027162**

Voltage (V)	220-240
-------------	---------

### Physical data

Max. Lamp Diameter (mm) - D	60
Lamp Length (mm) - C/L	103
Lamp dimension equal to filament lamp equivalent	Yes

