



# Data sheet | Item number: 2060-954/028-000

Board-to-Board Link; Pin spacing 4 mm; 4-pole; Length: 28 mm; white



[www.wago.com/2060-954/028-000](http://www.wago.com/2060-954/028-000)



## Item description

- Board-to-board link simplifies in-line assembly of LED modules
- Easy push-in termination and disconnection without push-button actuation

## Recommendation:

Only suitable for 2060-45x, not for 2060-40x.

## Data

### Electrical data

### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	63 V
Rated impulse voltage (III / 3)	2.5 kV
Rated voltage (III / 2)	160 V
Rated impulse voltage (III / 2)	2.5 kV



Rated voltage (II / 2)	320 V
Rated impulse voltage (II / 2)	2.5 kV
Rated current	9 A

### Approvals per UL 1977

Rated voltage per UL 1977 (factory wiring only)	250 V
Rated current per UL 1977 (factory wiring only)	9 A

### Connection data

Total number of potentials	4
Number of connection types	1
No. of poles	4

### Geometrical Data

Pin spacing	4 mm / 0.157 inch
Width	15.4 mm / 0.606 inch
Height	2.6 mm / 0.102 inch
Depth	28 mm / 1.102 inch

### Mechanical data

Mating cycles	10
Number of mating cycles	max. 10 mating cycles
Suitable	for SMD PCB Terminal Blocks with Push-button

### Material Data

Color	white
Material group	I
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0
Contact material	Copper alloy
Contact plating	silver-plated
Weight	0.93 g

### Environmental Requirements







Limit temperature range	-60 ... +105 °C
-------------------------	-----------------

## Commercial data


Country of origin	CN
GTIN	4055143303842
Customs Tariff No.	8536901000

## Approvals / Certificates

### Country specific Approvals

Logo	Approval	Additional Approval Text	Certificate name
	CCA DEKRA Certification B.V.	EN 60947	NTR NL-7724
	CCA DEKRA Certification B.V.	EN 60998	NTR NL-7725
	CCA DEKRA Certification B.V.	EN 60838	NTR NL-2168246
	KEMA/KEUR DEKRA Certification B.V.	EN 60838	2168246.01
	KEMA/KEUR DEKRA Certification B.V.	EN 60947	71-108183
	KEMA/KEUR DEKRA Certification B.V.	EN 60998	71-108181

### UL-Approvals

Logo	Approval	Additional Approval Text	Certificate name
	cURus Underwriters Laboratories Inc.	UL 1977	E45171-20111005



## Downloads

### Documentation

#### Additional Information

Technical explanations	Apr 3, 2019	pdf 3.6 MB	Download
------------------------	-------------	---------------	----------

---

### CAD/CAE-Data

#### CAD data

3D Download 2060-954/028-000		URL	Download
------------------------------	--	-----	----------

---

Subject to changes.