


manifold rail

VABM-L1-10S-G18-2

Part number: 566558
★ Core product range

FESTO



Data sheet

Feature	Value
Grid dimension	10.5 mm
Max. number of valve positions	16
Operating pressure	-0.9 ... 10 bar
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Authorisation	RCM Mark c CSA us (OL) c UL us - Recognized (OL)
Max. tightening torque, H-rail mounting	1.5 Nm
Max. tightening torque, valve mounting	0.45 Nm
Max. tightening torque, wall mounting	3 Nm
Product weight	66 g
Pneumatic connection, port 1	G1/8
Pneumatic connection, port 3	G1/8
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminium alloy