



RE620-LF

- Epoxy glass hard fabric FR4 1.50 mm
- Two-sided 35 μ m Cu
- Plated-through (PTH)
- Hot tinned (HAL lead free)
- Two raster fields with 7 x 37 soldering pads each (1.70 x 1.70 mm) in raster 2.54 mm (bore \varnothing 1.10 mm)
- One raster field with 25 x 75 soldering pads (0.70 x 0.70 mm) in raster 1.25 mm (bore \varnothing 0.30 mm)
- 37 three hole pads in raster 2.54 mm, which are transferred to a raster 1.25 mm
- One raster field with 25 x 75 soldering pads (1.70 x 1.70 mm) in raster 1.27 mm (bore \varnothing 1.10 mm)
- 37 three hole pads in raster 2.54 mm, which are transferred to a raster 1.27 mm
- Pre-scored predetermined breaking point
- Size 100 x 160 mm