

BRM 061813

- Part number : BRM 061813
- Profile / style : British 6 mm
- Connection : Hose barb for hose ID 13 mm
- Description : Compressed air coupling
- Maxi working pressure : 12 bar
- Maxi temperature : +70°C
- Flow @ 6 b with DP 0.6 bar : 750 l/min.
- Locking system : One push button
- Material : High resistance and corrosion resistant metal
- Profile color code : Orange
- Antistatic
- "Anti bursting" inside cartridge
- Silicon free
- Designed for severe applications
- High corrosion resistance
- Crush and shock resistant
- Positionable body
- "0 pressure drop" designed high flow valve

