





**φ 5.2x20 GLASS TUBE FUSES (FAST-BLOW)
OUTER SOLDERING**



(unit:mm)



I-T CHARACTERISTICS CURVE



ELECTRICAL CHARACTERISTICS:

RATING	2.1 In		2.75 In		4 In		10 In		
	Max	Min	Max	Min	Max	Max			
Blowing Time	$\ge 32mA-100mA$	30min	10ms	500ms	3ms	100ms	20ms		
	$> 100mA-6.3A$	30min	50ms	2s	10ms	300ms	20ms		

INTERRUPTING RATING:
35A OR 10 In WHICHEVER IS
GREATER
CCC/VDE/SEMKO

RATING

Catalog No.	Ampere Rating	RV Voltage (V)	Voltage Rating	Disjunction Power
1	100mA	3550	H/L	H/L
2	125mA	2100	H/L	H/L
3	150mA	2100	H/L	H/L
4	160mA	2000	H/L	H/L
5	200mA	1700	H/L	H/L
6	250mA	1400	H/L	H/L
7	300mA	1500	H/L	H/L
8	315mA	1300	H/L	H/L
9	350mA	1300	H/L	H/L
10	400mA	1200	H/L	H/L
11	500mA	1000	H/L	H/L
12	600mA	650	H/L	H/L
13	700mA	650	H/L	H/L
14	750mA	600	H/L	H/L
15	800mA	240	H/L	H/L
16	1A	200	H/L	H/L
17	1.2A	200	H/L	H/L
18	1.25A	200	H/L	H/L
19	1.5A	200	H/L	H/L
20	1.6A	180	H/L	H/L
21	1.6A	180	H/L	H/L
22	2A	170	H/L	H/L
23	2.5A	170	H/L	H/L
24	3A	150	H/L	H/L
25	3.15A	150	H/L	H/L
26	3.5A	150	H/L	H/L
27	4A	130	H/L	H/L
28	5A	130	H/L	H/L
29	6A	130	H/L	H/L
30	6.3A	130	H/L	H/L
31	7A	120	H/L	H/L
32	8A	100	H/L	H/L
33	10A	100	H/L	H/L
34	12A	100	H/L	H/L
35	15A	100	H/L	H/L

Ampere Voltage:
H Denotes For 250V
L Denotes For 125V

Disjunction Power:
H Denotes For High Disjunction
L Denotes For Low Disjunction

TOLERANCES UNLESS NOTED OTHERWISE X XX XXX 90° FORMED +20° ANGLES -1	DRAWN	MODEL NO.	CUSTOMER		
	DESIGN	FBGTF1019/20	CUSTOMER NO.		
	CHECKED	DWG NO.	VER	I:1	SCALE
	APPROVED	FBFUSE1052V1	UNIT	mm	SHEET
	DATE 07/16/25	Ningbo Best Group CO., LTD			
	CONTRACT NO.	www.fbelefuse.com Email:sales@fbelefuse.com			
	AGENCY APPROVAL	Tel:+86-574-87793491 Fax:+86-574-87792835			

