





**Φ 6.35x32, Φ 6.35x30 GLASS TUBE FUSES  
OUTER SOLDERING (FAST-BLOW)**



(unit:mm)



**I-T CHARACTERISTICS CURVE**



**ELECTRICAL CHARACTERISTICS:**

RATING	2.1 In		2.75 In		4 In		10 In	
	Max	Min	Max	Min	Max	Max	Max	
Blowing Time	$\geq 50mA-100mA$	20s	20ms	200ms	1ms	30ms	7ms	
	$> 100mA-10A$	20s	20ms	1500ms	5ms	400ms	80ms	

**INTERRUPTING RATING:**  
35A OR 10 In WHICHEVER IS  
GREATER  
CCC/VDE/SEMKO

**RATING**

Catalog No.	Ampere Rating	RV Voltage Drop	Voltage Rating	Disjunction Power
1	100mA	6000	H/L	H/L
2	125mA	5500	H/L	H/L
3	150mA	5000	H/L	H/L
4	160mA	5000	H/L	H/L
5	200mA	4000	H/L	H/L
6	250mA	3500	H/L	H/L
7	300mA	3000	H/L	H/L
8	315mA	3000	H/L	H/L
9	350mA	3000	H/L	H/L
10	400mA	2500	H/L	H/L
11	500mA	2000	H/L	H/L
12	600mA	1800	H/L	H/L
13	700mA	1800	H/L	H/L
14	750mA	1800	H/L	H/L
15	800mA	1500	H/L	H/L
16	1A	500	H/L	H/L
17	1.2A	400	H/L	H/L
18	1.25A	400	H/L	H/L
19	1.5A	400	H/L	H/L
20	1.6A	400	H/L	H/L
21	1.8A	400	H/L	H/L
22	2A	300	H/L	H/L
23	2.5A	250	H/L	H/L
24	3A	250	H/L	H/L
25	3.15A	250	H/L	H/L
26	3.5A	250	H/L	H/L
27	4A	250	H/L	H/L
28	5A	200	H/L	H/L
29	6A	200	H/L	H/L
30	6.3A	200	H/L	H/L
31	7A	200	H/L	H/L
32	8A	200	H/L	H/L
33	10A	200	H/L	H/L
34	12A	200	H/L	H/L
35	15A	200	H/L	H/L

**Ampere Voltage:**  
H Denotes For 250V  
L Denotes For 125V

**Disjunction Power:**  
H Denotes For High Disjunction  
L Denotes For Low Disjunction

TOLERANCES UNLESS NOTED OTHERWISE

X  
XX  
XXX  
90° FORMED +20°  
ANGLES -1



DRAWN	
DESIGN	
CHECKED	
APPROVED	
DATE	07/16/25
CONTRACT NO.	
AGENCY APPROVAL	

MODEL NO.  
**FBGTF1043/1044**  
DWG NO.  
**FBFUSE1063V1**

CUSTOMER			
CUSTOMER NO.			
VER	I:1	SCALE	
UNIT	mm	SHEET	

Ningbo Best Group CO., LTD  
www.fbelefuse.com Email:sales@fbelefuse.com  
Tel:+86-574-87793491 Fax:+86-574-87792835