


## Specification Sheet

Part Number: 553-50016

Slide Slit and optional center slits for easy wire insertion.  
Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.

A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.



ShrinkTrak Labels, 1-Sided, Unslit, .25" (6.35mm), PO-X, White, 250/box

**Article Number** 553-50016

**Type** HST6-2WH

**Color** White (WH)

**Quantity Per** box

**Product Description** HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production.

**Short Description** ShrinkTrak Labels, 1-Sided, Unslit, .25" (6.35mm), PO-X, White, 250/box

**Global Part Name** HST6-2WH-PO-X-WH

**Variant** Thin-Wall

**Width W (Imperial)** 1.9

**Width W (Metric)** 48.26

**Thickness T (Imperial)** .003

**Thickness T (Metric)** .0762

**Height H (Imperial)** 0.42

**Height H (Metric)** 10.67

**Width of Liner (Metric)** 76.2

**Width of Liner (Imperial)** 3.0

**Outside Diameter OD (Imperial)** 0.25

**Outside Diameter OD (Metric)** 6.35

**Outside Diameter Max (Imperial)** 0.25

**Outside Diameter Max (Metric)** 6.35

**Wall Thickness WT (Imperial)** 0.028

**Wall Thickness WT (Metric)** 0.71

|                                     |  |
|-------------------------------------|--|
| <b>Material</b>                     | Polyolefin, cross-linked (PO-X)  |
| <b>Material Shortcut</b>            | PO-X   |
| <b>US MIL SPEC</b>                  | MIL-STD-202G Method 215K<br>SAE-AS81531<br>SAE-AMS-DTL-23053/5 Class 1 and 3   |
| <b>Flammability</b>                 | UL 224 VW-1  |
| <b>Halogen Free</b>                 | No   |
| <b>Operating Temperature</b>        | -67°F to +275°F (-55°C to +135°C)  |
| <b>Reach Compliant (Article 33)</b> | Yes  |
| <b>ROHS Compliant</b>               | Yes  |
| <b>Certification/Specification</b>  | SAE - AS81531 SAE - AMS - DTL-23053/5 Class 1 and 3 UL 224<br>125 °C 600V VW-1 |
| <b>Package Quantity (Imperial)</b>  | 250  |
| <b>Package Quantity (Metric)</b>    | 250  |
| <b>Customs Number</b>               | 3917320000   |
| <b>Labels per Column</b>            | 1  |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-50016](#)