

## Coaxial Cable Connector 16\_QMA-50-2-2/133\_N

### Description

Right angle cable plug

Interface standards  
QMA QLF compliant



### Technical Data

#### Electrical Data

Impedance	50 Ω	
Interface frequency max.	18 GHz	
Frequency range	DC to 2 GHz	2 to 2.5 GHz
Return loss	32 dB	30 dB

#### Mechanical Data

Centre contact	soldered
Outer contact	crimped
Weight	0.0071 kg

#### Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00006286
Catalogue drawing	DOU-00006288
Assembly instruction	DOC-0000178735

### Ordering Information

Bulk 100 pcs package	16_QMA-50-2-2/133_NH
Single package	16_QMA-50-2-2/133_NE

### Additional Information

Suitable cables	RG_316_U, ENVIROFLEX_316, RG_188_A/U, RG_174_U
-----------------	--

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[16\\_QMA-50-2-2/133\\_NE](#)