

MOSA M12 MALE 0° FIELD-WIREABLE (IDC)

4-pol., 0,14-0,34mm², shielded


Male straight

4-pole

Connection cross section: 0.14...0.34 mm²

[Link to Product](#)

Illustration



Male



Product may differ from Image

Approvals



Form

Form 12551

Technical Data

| | |
|-------------------------------|--|
| Operating voltage | max. 50 V AC/DC |
| Operating current per contact | max. 4 A |
| Connection cross section | 0.14...0.34 mm ² (conductor diameter min. 0.1 mm) |
| Sealing range (cable Ø) | 5.5...7.2 mm |
| Wire isolation | PVC, PP |
| Outer wire Ø | 1.2...1.6 mm |
| Protection | IP67 inserted and tightened (EN 60529) |

General data

| | |
|----------------------|-----------------|
| Temperature range | -25...+85 °C |
| Dimensions H × W × D | 52×19.5×19.5 mm |

Commercial data

| | |
|------------------------|----------|
| country of origin | DE |
| customs tariff number | 85369010 |
| minimum order quantity | 1 |