



Traitement de surface svt CdC BEP003
Surface treatment according : CDC
BEP003

Tolérances générales découpe (pliage ITx2)
General tolerances for cutting (bending ITx2)

Thickness	0.1 < D < 10	10 < D < 63	63 < D < 400	400 < D < 1000	1000 < D < 3000
0.1 < T < 3	±0,2	±0,3	±0,5	±1	±2
3 < T < 6	±0,25	±0,4	±0,6	±1,5	±3
Angles	±2°	±3°			

2	1	BROCHE MOLETEE	INOX 316L (1.4404)		0.00 kg	538.92 mm ²
1	2	COTE CH 40x60 TROUS FRAISES	PA 6-6 + 30% FV NOIR		0.01 kg	7125.10 mm ²
Rep Item	Qté Qty	DESIGNATION Description	Matière Material	TRAITEMENT	Poids Weight	Surface Surface

Désignation : Charnière 40x120 A TROUS FRAISES Title :			Feuille/Sheet : 1/1 Format : A3 Echelle : 1:1 Scale :		La solution charnière et verrouillages
Dessiné par : ATY Drawn by :	le : 07/07/2021 date :	Poids total : 0.02 Kg Total weight :	FORM BEP 008 K		
Vérifié par : BBM Verified by :	le : 07/07/2021 date :				

A	07/07/2021	Création	ATY	BBM
Ind.	Date	Modifications	Des.	Ver.