

ISO 9001:2000

Model # BU-2020-A-**-*

- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: hands free testing at 300V, 10 Amps

CHECK INVENTORY

Insulated Alligator Clip to Stackable Banana Plug



Model # BU-2030-A-**-*

- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Alligator Clip: nickelplated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red
- Rating: hands free testing at 300V, 10 Amps

Insulated Mini-Alligator Clip to Stackable Banana Plug



Model # BU-2031-A-**-*

- Material: Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring; Alligator Clip: nickelplated steel with PVC insulator; Hook-up Wire: #20 (41/36) AWG tinned copper with 105°C PVC insulation
- **Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red

Rating: hands free testing at 300V, 10 Amps

CHECK INVENTORY

Multiple Feature Test Prod to Right Angle Shrouded Banana Plug



- Material: Needle: stainless steel; Banana plugs: nickelplated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 1000V Category II, 20 Amps

CHECK INVENTORY

Shrouded Right Angle Banana Plug



Model # BU-2243-D-48-*

- The stainless steel probe is Teflon® insulated except for the working end to prevent unwanted contact with other components that may be in the way
- Material: Needle: stainless steel; Banana Plugs: nickelplated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 600V Category II, 20 Amps

CHECK INVENTORY

Multiple Feature Test Prod to Unshrouded Banana Plug



Model # BU-2641-D-48-*

- Material: Needle: stainless steel; Banana Plugs: nickelplated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 600V Category II, 10 Amps

CHECK INVENTORY

Multiple Feature Test Prod to Unshrouded Banana Plug



Model # BU-2741-D-48-*

- Material: Needle: stainless steel; Banana plugs: nickelplated brass; Housing: ABS; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- *Std. Colors: -0 Black, -2 Red
- Rating: 600V Category II, 10 Amps

CHECK INVENTORY

Unshrouded Banana Plugs on Both Ends "C Ultra-Flex-Silicone



Model # BU-2929-M-**-*

- Material: Unshrouded Banana Plugs: Mueller No. Bu-16-*; Hook-up wire: #18 AWG (65/36) tinned copper with 90°C PVC insulation
- **Length: -10" (.25m), 20" (.5m), 39" (1m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 3 kV, 20 Amps

CHECK INVENTORY

Shrouded Banana Plug to Safety Test Prod "C Silicone



Model # BU-4061-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring. Probe: stainless steel tip with 8-32 UNC thread. Hook up wire: #18 AWG, silicone insulator.
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue.
- Rating: 1000V, 20 Amps, IEC 1010 compliant

CHECK INVENTORY

Shrouded Right Angle Banana Plug to Safety Test Prod - Silicone



Model # BU-4062-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring. Probe: stainless steel tip with 8-32 UNC thread. Hook up wire: #18 AWG, silicone insulator.
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue.
- Rating: 1000V, 20 Amps, IEC 1010 compliant

CHECK INVENTORY

Stackable 0.080" (2.0mm) Pin Plug on Both Ends



Model # BU-4444-A-**-*

- Tip jack accepts 0.080" (2.0mm) diameter pin jack contact
- Material: Pin Plug: 0.080" (2.0mm) diameter;
 0.500" (12.7mm) long, nickel-plated brass pin tip, nickel-plated beryllium copper spring, ABS housing.
 Hook-up Wire: #22 (19/34) AWG tinned copper with 105°C PVC insulation
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red
- Rating: Hands free testing at 300VAC, 15 Amps

CHECK INVENTORY

Shrouded Banana Plug on Both Ends "C Silicone



Model # BU-6161-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring. Hook up wire: #18 AWG, silicone insulator
- *Std Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 20 Amps, IEC 1010 Compliant

CHECK INVENTORY

Right Angle Shrouded Banana Plug to Shrouded Banana Plug "C Silicone



Model # BU-6162-M-**-*

- Material: Banana plugs: nickel-plated brass body, nickel-plated beryllium copper spring; Hook up wire: #18 AWG, silicone insulator
- *Std. Colors: -0 Black, -2 Red, -4 Yellow, -6 Blue
- Rating: 1000V, 20 Amps, IEC 1010 Compliant

CHECK INVENTORY

Stackable Dual Banana Plug to Mini-Micro-Plunger with RG58



Model # BU-7014-B-**-*

- Material: Plunger: nylon housing, stainless steel spring and beryllium copper contact. Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300 VRMS

Stackable Dual Banana Plug to Stackable Single Banana Plug with RG58



Model # BU-7020-B-**-*

- Material: Single Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nineleaf cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m)

- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 500 VRMS

Stackable Dual Banana Plug to Mini-Alligator Clip with RG58



Model # BU-7031-B-**-*

- Material: Alligator clip: nickel-plated steel with PVC insulator. Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300 VRMS

CHECK INVENTORY

Stackable Dual Banana Plug to Stackable Pin Plug with RG58



Model # BU-7044-B-**-*

- Material: Pin Plug: 0.080" (2.0mm) diameter;
 0.500" (12.7mm) long, nickel-plated brass pin tip, nickel-plated beryllium copper spring, ABS housing.
 Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring.
 Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm
- Length: -12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 500 VRMS

Stackable Double Banana Plug on Both Ends with RG58



Model # BU-7070-B-**-*

 Material: Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf

- cage spring. Coaxial Cable: Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300 VRMS

Shrouded Double Banana Plug on Both Ends with RG58



Model # BU-7171-B-**-0

- Material: Double Banana Plug: ABS housing, brass body and beryllium copper, nickel-plated, nine-leaf cage spring. Coaxial Cable: Shielded #22 AWG (7/30) twisted pair with drain connected to (-) side of one banana plug; side with drain connection is marked. Shielded RG58C/U, MIL-C-17F, 50 ohm.
- Length: -12" (.3m), 24" (.6m), 36" (.9m), 48" (1.2m), 60" (1.5m)
- Rating: Hands free testing at 500 VRMS

CHECK INVENTORY

0.025in(0.6mm) Square Pin Receptacle - Both Ends



Model

BU-8080-E-**-*

- Material: Pin Receptacle: ABS housing, 0.025" (0.6mm) copper-nickel-tin alloy 725 with 0.000030" (0.00076mm) gold contact plating conductor. Hook-up Wire: #22 AWG (19/34) tinned copper with 105°C PVC insulation.
- Length: -6" (.15m), 12" (.3m), 24" (.6m), 36" (.9m)
- *Std. Colors: -0 Black, -2 Red.
- Rating: Hands free testing at 300V, 3 Amp

CHECK INVENTORY

© 2005 Mueller Electric Company, Inc.

Home | Products | Check Order Status | About Us | Contact Us | Request a Catalog | Site Map