


OD6025-IP68 Series



DC Fan, 12, 24, 48V
60x25mm (2.36" x 1.0")



Frame	PBT, UL94 V-0 plastic	Operating Temperature -15°C ~ +65°C Storage Temperature -25°C ~ +70°C Life Expectancy 60,000 hours (L10 at 45°C) Available Options Tachometer Alarm PWM 5V Available Weight: 0.14 lbs m0	
Impeller	PBT, UL94 V-0 plastic		
Connection	2x Lead wires 24 AWG		
Motor	Brushless DC, Auto Restart, Polarity Protected, Electronically Protected, IP68		
Bearing System	Dual Ball Bearings		
Dielectric Strength	500VAC/min		
Insulation Resistance	10M ohm between leadwires and frame (500 VDC)		

Part Number	Rated Voltage	Input Power	Rated Current	Rated Speed (RPM)	Airflow (CFM)	Noise Level (dB)	Max. Static Pressure
OD6025-12HHBIP68	12 VDC	1.8 W	0.15 A	4400	32	32	0.24"H ₂ O
OD6025-12HBIP68	12 VDC	1.8 W	0.15 A	4000	25	30	0.22"H ₂ O
OD6025-12MBIP68	12 VDC	1.5 W	0.12 A	3200	17	25	0.16"H ₂ O
OD6025-12LBIP68	12 VDC	1.0 W	0.08 A	2500	14	20	0.14"H ₂ O
OD6025-24HHBIP68	24 VDC	2.8 W	0.12 A	4400	32	32	0.24"H ₂ O
OD6025-24HBIP68	24 VDC	2.8 W	0.12 A	4000	25	30	0.22"H ₂ O
OD6025-24MBIP68	24 VDC	2.2 W	0.09 A	3000	17	25	0.16"H ₂ O
OD6025-24LBIP68	24 VDC	1.5 W	0.06 A	2500	14	20	0.14"H ₂ O
OD6025-48HHBIP68	48 VDC	3.4 W	0.07 A	4400	32	32	0.24"H ₂ O
OD6025-48HBIP68	48 VDC	3.4 W	0.07 A	4200	28	30	0.23"H ₂ O

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Orion Fans:

[OD6025-24MBIP68](#) [OD6025-12HHBIP68](#) [OD6025-12LBIP68](#) [OD6025-24HHBIP68](#) [OD6025-12HBIP68](#) [OD6025-48HHBIP68](#) [OD6025-24HBIP68](#) [OD6025-24LBIP68](#) [OD6025-48HBIP68](#) [OD6025-12MBIP68](#)