


## RKMCK

PICO (M8) Field Attachable Connector, Female Straight, Screw Termination, 3 and 4 pole, 60V AC/75V DC, Cable Range 3.5 - 5mm, brass coupling nut, for Wire Size from 26AWG up to 20 AWG, IP 67 / NEMA 6P Rated.



### Technical Data

#### Material

Insert	PUR
Contact	Brass, gold over nickel plated
Body	Brass, over nickel

#### Electrical

Current Rating	3A
Voltage Rating	60 V AC / 75 V DC

#### Mechanical

Temperature	-40°C to + 85°C
Protection	IP 67, NEMA 6P
Termination	Terminal Screws
Max. Wire Size	0.14 - 0.5mm <sup>2</sup> max



### Features & Benefits

IP67/NEMA 6P rated. Easy assembly with screw terminals. Wire gauges from 0.14mm<sup>2</sup> to 0.50mm<sup>2</sup> (26 AWG to 20 AWG). Gold over nickel plated brass contacts. Cable exit allowing cable OD from 3.5 mm to 5mm (.138" to .197").

### Face Views / Pin Color Code

3P Female

4P Female



### Part Number

### Poles

### Gender

RKMCK 3	<b>3</b>	<b>Female</b>
RKMCK 4	<b>4</b>	