



Click [here](#) for the 3D model.

### Dimensions

D	55mm MAX
T	55mm MAX
H	35mm MAX
LL	4mm +/-1mm
S	26mm NOM
S1	35mm NOM
Wire Size	2.3mm

### Packaging Specifications

Packaging	Tray
Packaging Quantity	48
Component Weight	113.1 g

### General Information

Series	SCR38
Style	Through-Hole
RoHS	Yes
Notes	Lead Spacing (S/S1) Are For Reference Only.
Miscellaneous	Temperature Rise Maximum: 45 K.
Core	Mn-Zn Ferrite

### Specifications

Voltage AC	500 VAC
Inductance	1 mH
Current	20 A
Temperature Range	-25/+120°C
DC Resistance	3.4 mOhms