

## TA 1220 compact tachometers - 8 mm display

LED tachometers with red 4-digit 8 mm LED. Displays speed, rate and frequency. NPN, PNP, NAMUR, TTL or sinusoidal pulsed input signal  $10 \rightarrow 600$  Vac. Displayed in seconds, minutes or hours. 2 alarms with relay outputs. Measuring principle based on measurement of the input signal period. IP65 front panel protection. Mounting bracket supplied.

Manufacturer's reference:		Supply range:	
TA1220.014AX01		$85 \rightarrow 265$ Vac and $100 \rightarrow 300$ Vdc	
TA1220.015AX01		$10.5 \rightarrow 70$ Vdc and $21 \rightarrow 53$ Vac	
Control input:	Compatible by programming NPN, PNP, Namur, TTL or sine		
Pulse input	$5 \rightarrow 24 \text{ Vdc}$		
Sine input	$10 \rightarrow 600 \text{ Vac}$		
Frequency	0.01 Hz $\rightarrow$ 7 kHz		
Breaking capacity	260 Vac / 1 A / 150 VA		
Consumption	4 W		
Dimensions	24 x 48 x 125 mm		
Cut-out	22 x 45 mm		

Panel Mounting 24 x 48-Rate- Frequency - Tachometers