

[Request more info](#)

Part Number : 5988360117F



[Surface Mount LED Selector Guide](#)

### General Description

Lens Color	Water Clear
Series	598
Description	SM LED 1208 ALINGAP 7 REEL
Package Options	7" reel 3,000pcs / reel
Viewing Angle	160°

### Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	20mA
Reverse Voltage	5v
Operating Temperature	-40~+100 °C
Storage Temperature	-40~+100 °C

### Operating Characteristics

Color	Yellow-Green
Power Dissipation Max	48nW