



JKL LAMP PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF22140-24B	LCD HIGH OUTPUT WHITE 8400°k RGB	730 @ 0°C	340	5	38,000 ± 10%	20,000

\* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

				<b>METRIC</b> DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0 ANGLE +/- 0							
		THIRD ANGLE PROJECTION				<b>TITLE</b> MINIATURE COLD CATHODE FLUORESCENT LAMP					
<b>A</b> DIM LINE CORRECT. AND 140 +/- 5.0 TO 140 +/- 3.0 RELEASED		10/17/00 L. WENGSTROM		APPVD BY DATE FD 10/17/00		SIZE <b>A</b> FSCM NO. <b>55335</b>		DRAWING NO. <b>BF22140-24B</b>			
REV. NO.		DESCRIPTION/ECO NUMBER		APPVD DATE		SCALE NONE		RELEASED DATE 6/7/00		REVISION DATE 10/17/00	
				- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED				REV. NO. <b>A</b>		SHEET <b>1</b> OF <b>1</b>	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF22140-24B](#)